



Pass and Seymour  
20A 125V Dual-Controlled Plug Load Decorator Duplex Receptacle, Gray  
Part No. 26352CDGRY



This durable, dependable Plug Load receptacle is designed to help you meet ASHRAE energy standards. The controlled marking printed on the tough nylon face is both NEMA-approved and compliant with the National Electrical Code.

## Features & Benefits

NEMA approved controlled receptacle marking pad printed on the face of receptacle for superior abrasion resistance.	Can be used to control loads using the Wattstopper DLM system and other building control systems.
Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.	One-piece, brass, triple-wipe power contacts for lasting retention.
Heavy-duty compact design for easier installation and long lasting performance.	Terminal compartments isolated from each other for positive conductor containment.
Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.	All devices fit standard #26 opening wall plate.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007032901	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Energy Saving On/Off
Application Sector	Commercial	Standard	FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Outlet

### Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

---

Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

Technical Information

---

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

---

Indoor/Outdoor	Indoor
----------------	--------

---