



Heavy-Duty Decorator Spec Grade Duplex Receptacle Back & Side Wire 15amp 250volt Ivory

## Features & Benefits

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.

Heavy-duty compact design for easier installation and long lasting performance.

Impact-resistant nylon face.

Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.

Tri-drive terminal and mounting screws.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

One-piece, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Terminal compartments isolated from each other for positive conductor containment.

All devices fit standard #26 opening wall plate.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Color	Ivory	UPC Number	785007785883
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Standard	UL 498

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

---

## Technical Information

---

Number of Poles	Double Pole	Voltage	250 V
Phase	3	Wire Size	10-14Awg
Number of Wires	3		

---