



Heavy-Duty Decorator Spec Grade Single Receptacle Back & Side Wire 15amp 250volt White



Features & Benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body. One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face. Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire. All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws. Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents. For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Color	Gray	UPC Number	785007786033
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Standard	UL 498

Listing Agencies / 3rd Party Agencies

cUL Listed	Yes	cUL ListingNumber	140596
------------	-----	-------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	250 V
Phase	3	Wire Size	10-14Awg
Number of Wires	3		
