



Heavy-Duty Decorator Spec Grade Single Receptacle Back & Side Wire 15amp 250volt White

Features & Benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body. One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face. Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire. All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws. Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents. For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

| | | | |
|--------------------|------------------------|--------------|----------------|
| Color | Ivory | UPC Number | 785007786040 |
| Country Of Origin | Mexico | Product Line | Pass & Seymour |
| Application Sector | Residential/Commercial | Standard | UL 498 |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|-------------------|--------|
| cUL Listed | Yes | cUL ListingNumber | 140596 |
|------------|-----|-------------------|--------|

Technical Information

| | | | |
|-----------------|-------------|-----------|----------|
| Number of Poles | Double Pole | Voltage | 250 V |
| Phase | 3 | Wire Size | 10-14Awg |
| Number of Wires | 3 | | |
