



Locking Dust-Tight Rubber Plug, 20amp 3480, NEMA Configuration L16-20

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather

Quick lead assembly screws aid in a fast installation

Keyed body and cover for easy assembly and alignment

Two Screw cable clamp secures wire and provides superior strain relief

Industrial strength, brass blades and contacts resist heat rise while providing excellent conductivity

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007032918	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

Technical Information

Phase	Three	Number of Wires	4
Number of Poles	3-Way	Wire Size	14 AWG min - 10 AWG max

Voltage

480 V

Environmental Conditions

Moisture Resistance NEMA 4,
4X, 12, 6, 6P/IP65, 66, 67 (Plug
& Connector only)
Flammability UL94V0 (boxes &
wiring device interiors)
Operating Temperature -40°C
(without impact) to +60°C
continuous UV resistance All
exposed materials are UV
stabilized
