



□ Heavy-Duty Decorator Spec Grade Single Receptacle Back & Side Wire 20amp 250volt Ivory

## Features & Benefits

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.	One-piece, brass, triple-wipe power contacts for lasting retention.
Heavy-duty compact design for easier installation and long lasting performance.	Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
Impact-resistant nylon face.	Terminal compartments isolated from each other for positive conductor containment.
Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.	All devices fit standard #26 opening wall plate.
Tri-drive terminal and mounting screws.	Auto-ground clip assures positive ground.
For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, <a href="#">click here</a> .
Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL498, cUL CSA		

### Dimensions

Product Width US	1.322 in	Product Depth US	1.188 in
Product Length US	2.635 in		

### Listing Agencies / 3rd Party Agencies

cUL ListingNumber	140596	cUL Listed	Yes
-------------------	--------	------------	-----

### Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	250.0 V
Environmental Conditions	Flammability: UL94 V2		