



Heavy-Duty Decorator Spec Grade Single Receptacle Back and Side-Wire 20A 250V



Features & Benefits

Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.

Heavy-duty compact design for easier installation and long lasting performance.

Impact-resistant nylon face.

Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.

Tri-drive terminal and mounting screws.

For covering patents, see www.legrand.us/patents.

One-piece, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Terminal compartments isolated from each other for positive conductor containment.

All devices fit standard #26 opening wall plate.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007786590
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	UL 498		

Listing Agencies / 3rd Party Agencies

cUL Listed	Yes
------------	-----

Technical Information

Phase	3	Number of Wires	3
-------	---	-----------------	---

Number of Poles

Double Pole

Wire Size

10-14Awg

Voltage

250 V
