



## Pass and Seymour 26W47 Watertight NEMA 4X/6P Locking Plug, Yellow Part No. 26W47



Locking Watertight Plug, 20amp 125volt, NEMA Configuration L5-20, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P & IP67 rated.

### Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color coded sealing bushings provided for large range of cord diameters

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

### Specifications

#### General Info

Color	Yellow	UPC Number	785007032611
Country Of Origin	United States	Product Line	Pass & Seymour
Standard	UL Listed, CSA Listed		

#### Technical Information

Number of Poles	Double Pole	Voltage	125 V
Phase	Single	Wire Size	14 AWG min - 10 AWG max
Number of Wires	3	Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed materials are UV stabilized