



Pass and Seymour
Watertight NEMA 4X/6P Locking Plug, 20A 250V, Yellow
Part No. 26W48



Locking Watertight Plug, 20 amp 250 volt, NEMA Configuration L6-20, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P & IP67 rated.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated

Devices resist high-pressure hose down of 1,500 psi

Color coded sealing bushings provided for large range of cord diameters

Large ribs on body for a superior grip when mating

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007033120	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

Technical Information

Phase	Single	Number of Wires	3
Number of Poles	Double Pole	Wire Size	14 AWG min - 10 AWG max

Voltage

250 V

Environmental Conditions

Moisture Resistance NEMA 4,
4X, 12, 6, 6P/IP65, 66, 67 (Plug
& Connector only)
Flammability UL94V0 (boxes &
wiring device interiors)
Operating Temperature -40°C
(without impact) to +60°C
continuous UV resistance All
exposed material s are UV
stabilized
