



Locking Dust-Tight Rubber Connector, 20amp 125/250V, Non-NEMA Configuration.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather Two Screw cable clamp secures wire and provides superior strain relief

Quick lead assembly screws aid in a fast installation

Industrial strength, brass blades and contacts resist heat rise while providing excellent conductivity

Keyed body and cover for easy assembly and alignment

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	Yellow
UPC Number	785007033274
Country Of Origin	United States
Product Line	Pass & Seymour
Standard	UL Listed, CSA Listed

Technical Information

Number of Poles	3-Way
Voltage	125 V
Phase	Single
Wire Size	14 AWG min - 10 AWG max
Number of Wires	3

Environmental Conditions Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized