



Pass and Seymour
20A, 3° 480V Turnlok® Watertight Connector, NEMA 4X/6P, Yellow
Part No. 27W76



Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat and weather.

Multi-point sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color-coded sealing bushings provided for large range of cord diameters

For Covering Patents, see www.legrand.us/patents.

Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

Devices resist high-pressure hosedown of 1,500 psi.

Large ribs on body for a superior grip when mating.

Specifications

General Info

| | | | |
|--------------|-----------------------|-------------------|---------------|
| Product Line | Pass & Seymour | Color | Yellow |
| UPC Number | 785007032932 | Country Of Origin | United States |
| Standard | UL Listed, CSA Listed | | |

Technical Information

| | | | |
|-----------------|-------|-----------------|-------------------------|
| Phase | Three | Number of Wires | 4 |
| Number of Poles | 3-Way | Wire Size | 14 AWG min - 10 AWG max |

Voltage

480 V

Environmental Conditions

Moisture Resistance NEMA 4,
4X, 12, 6, 6P/IP65, 66, 67 (Plug
& Connector only)
Flammability UL94V0 (boxes &
wiring device interiors)
Operating Temperature -40°C
(without impact) to +60°C
continuous UV resistance All
exposed material s are UV
stabilized
