

Cyan 280-0469-00 Compatible 10GBase-CWDM SFP+ Transceiver (SMF, 1590nm, 80km, LC Duplex, DDM, I-Temp)



## Features & Benefits

**Guaranteed Compatible**  
In System tested in over 90 OEM switches, routers and servers.

**Industry Leading Lifetime Warranty**  
For more information by product line, visit our Warranty page.

**Full Service Technical Support**  
Call, chat, email or meet for expert optical connectivity support.

**99.98% Reliability Rate**  
Functionally, optically and environmentally tested to exact specifications.

**98% On-Time Delivery Rate**  
Extensive inventory guarantees same day shipping.

## Specifications

### General Info

Product Line	Ortronics	Country Of Origin	China
Type	Transceiver		

### Technical Information

Fiber Optic Cable Type	Single-Mode	Operating Temperature Min	-40 C
Operating Temperature Max	85 C	Data Transfer Rate	10 Gbps
Connector Type	LC Duplex	Form Factor	SFP+