

Nokia 3AL82027AA Compatible 10GBase-SR SFP+ Transceiver (MMF, 850nm, 300m, LC Duplex, DDM, I-Temp)



Features & Benefits

Guaranteed Compatible
In System tested in over 90 OEM switches, routers and servers.

Industry Leading Lifetime Warranty
For more information by product line, visit our Warranty page.

Full Service Technical Support
Call, chat, email or meet for expert optical connectivity support.

99.98% Reliability Rate
Functionally, optically and environmentally tested to exact specifications.

98% On-Time Delivery Rate
Extensive inventory guarantees same day shipping.

Specifications

General Info

Product Line	Ortronics	Country Of Origin	China
Type	Transceiver		

Technical Information

Fiber Optic Cable Type	Single-Mode	Operating Temperature Min	-40 C
Operating Temperature Max	85 C	Data Transfer Rate	10 Gbps
Connector Type	LC Duplex	Form Factor	SFP+