



Locking Dust-Tight Rubber Plug, 30amp 277volt, NEMA Configuration L7-30

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather Two Screw cable clamp secures wire and provides superior strain relief

Quick lead assembly screws aid in a fast installation

Industrial strength, brass blades and contacts resist heat rise while providing excellent conductivity

Keyed body and cover for easy assembly and alignment

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color Yellow

UPC Number 785007033649

Countries Of Origin United States

Product Line Pass & Seymour

Standard UL Listed, CSA Listed

Technical Information

Number of Poles Double Pole

Voltage 277 V

Phase Single

Wire Size 14 AWG min - 10 AWG max

Number of Wires 3

Environmental Conditions Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed materials are UV stabilized