



Pass and Seymour
28W77 Watertight,NEMA 4X/6P Locking Plug, Yellow
Part No. 28W77



Locking Watertight Plug, 30amp 3Y 600volt, L17-30 configuration, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P & IP67 rated.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color coded sealing bushings provided for large range of cord diameters

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007033403	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

Technical Information

Phase	Single	Number of Wires	4
Number of Poles	3-Way	Wire Size	12 AWG min - 6 AWG max

Voltage

600 V

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only)
Flammability UL94V0 (boxes & wiring device interiors)
Operating Temperature -40°C (without impact) to +60°C
continuous UV resistance All exposed materials are UV stabilized
