



Locking Dust-Tight Rubber Connector, 30amp 3Y600, NEMA Configuration L17-30.

## Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather Two Screw cable clamp secures wire and provides superior strain relief

Quick lead assembly screws aid in a fast installation

Industrial strength, brass blades and contacts resist heat rise while providing excellent conductivity

Keyed body and cover for easy assembly and alignment

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

**Color** Yellow

**UPC Number** 785007032970

**Countries Of Origin** United States

**Product Line** Pass & Seymour

**Standard** UL Listed, CSA Listed

### Technical Information

**Number of Poles** 3-Way

**Voltage** 600 V

**Phase** Three

**Wire Size** 12 AWG min - 6 AWG max

**Number of Wires** 4

**Environmental Conditions** Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed materials are UV stabilized