



Pass and Seymour
Turnlok® Watertight NEMA 4X/6P Locking Connector, Yellow
Part No. 29W47



Locking Watertight Connector, 30amp 125volt, NEMA Configuration L5-30, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color coded sealing bushings provided for large range of cord diameters

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007032604	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

Dimensions

Product Width US	2.35 in	Product Length US	4.75 in
------------------	---------	-------------------	---------

Technical Information

Phase	Single	Number of Wires	3
Amperage	30 A	Number of Poles	Double Pole

Wire Size	14 - 10 AWG	Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized
-----------	-------------	--------------------------	---
