



Pass and Seymour  
**29W77 Watertight NEMA 4X/6P Locking Connector, Yellow**  
Part No. 29W77



Locking Watertight Connector, 30amp 3Y 600volt, NEMA Configuration L17-30, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

## Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather.

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

Color coded sealing bushings provided for large range of cord diameters

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Devices resist high-pressure hose down of 1,500 psi.

Large ribs on body for a superior grip when mating.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007033731	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

### Technical Information

Phase	Single	Number of Wires	4
Number of Poles	3-Way	Wire Size	12 AWG min - 6 AWG max

---

Voltage

600 V

Environmental Conditions

Moisture Resistance NEMA 4,  
4X, 12, 6, 6P/IP65, 66, 67 (Plug  
& Connector only)  
Flammability UL94V0 (boxes &  
wiring device interiors)  
Operating Temperature -40°C  
(without impact) to +60°C  
continuous UV resistance All  
exposed material s are UV  
stabilized

---