



15A/125A Trademaster® Duplex Receptacle

Features & Benefits

Quality Materials, durability, and time-tested design

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Residential, Self-Grounding
Application Sector	Residential	Standard	UL498, CSA C22.2 No. 42
Type	Outlet		

Dimensions

Product Width US	1.32 in	Product Depth US	0.96 in
Product Height US	3.31 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Connection	push wire, Side wire	Number of Wires	3
------------	----------------------	-----------------	---

Temperature Rating	-30° - 60° C	Amperage	15 A
--------------------	--------------	----------	------

Number of Poles	Double Pole	Wire Size	14 - 12 AWG
-----------------	-------------	-----------	-------------

Indoor/Outdoor	Indoor	Voltage	125.0 V
----------------	--------	---------	---------

Environmental Conditions	Flammability: UL94 V2
--------------------------	-----------------------
