



Pass and Seymour  
Trademaster® 15A 125V Tamper-Resistant Duplex Receptacle, White  
Part No. 3232TRW



15A/125A Trademaster® Tamper-Resistant Duplex Receptacle

## Features & Benefits

Quality Materials, durability, and time-tested design

Rated 15 amperes

Wire Size: #12 - #14 AWG, Solid wire

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007240276
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Self-Grounding, Tamper-Resistant	Application Sector	Commercial, Residential
Standard	UL 498	Type	Outlet

### Dimensions

Product Width US	1.32 in	Product Depth US	1.0 in
Product Height US	3.31 in		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

## Additional Information

---

Product Environmental Profile Yes

---

## Technical Information

---

Is Tamper-Resistant	Yes	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 12 AWG
Indoor/Outdoor	Indoor		

---