



Pass and Seymour
Trademaster® 15A 125V Tamper-Resistant Weather-Resistant Duplex Receptacle, Ivory
Part No. 3232TRWRI



15A/125A Weather-Resistant Duplex Receptacle,

Features & Benefits

Quality Materials, durability, and time-tested design

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Wire Size: #12 - #14 AWG, Solid wire

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007241822
Country Of Origin	Mexico	Number of Receptacles	2
Features	Weatherproof	Outlet Type	Tamper-Resistant, Weather-Resistant
Application Sector	Hospitality, Residential	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.32 in	Product Depth US	1.0 in
Product Height US	3.31 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

Product Environmental Profile Yes

Technical Information

Is Tamper-Resistant	Yes	Connection Location	Side Only
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 12 AWG
Indoor/Outdoor	Outdoor	Wire Connection Type	Push Wire, Screw Terminals
Voltage	125.0 V		