

LOCK GG PLUG NON-NEMA 2P3W 30A 250V



## Features & Benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.

Raised ribs provide non-slip gripping profile for turning to lock and unlock.

Impact- and corrosion-resistant durable nylon 6 shell material.

Scallop shell design provides non-slip gripping surface for insertion and withdrawal.

New-design external cord grips provide visible assurance of safe and proper cord retention.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.

Double dovetail design provides superior protection against cord pull-out forces.

Rounded back contour reduces snags and hang-ups on the job site.

Visible stamped NEMA configuration and device rating.

Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007121001	Country Of Origin	United States
Application Sector	Industrial	Standard	UL Listed
Type	Plug Tail		

### Dimensions

Product Width US	1.5 in	Product Length US	1.9 in
------------------	--------	-------------------	--------

### Technical Information

Phase	Three	Number of Wires	3
Amperage	30 A	Number of Poles	Double Pole