



Pass and Seymour  
30A Non-NEMA 3 Wire Plug - Black Back, White Front Body  
Part No. 3331SS

Plug 3-Wire 30A 125/250V



## Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.	Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
Raised ribs provide non-slip gripping profile for turning to lock and unlock.	Double dovetail design provides superior protection against cord pull-out forces.
Impact- and corrosion-resistant durable nylon 6 shell material.	Rounded back contour reduces snags and hang-ups on the job site.
Scallop shell design provides non-slip gripping surface for insertion and withdrawal.	Visible stamped NEMA configuration and device rating.
New-design external cord grips provide visible assurance of safe and proper cord retention.	Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007333114	Country Of Origin	Mexico
Features	Locking	Application Sector	Industrial
Standard	UL498, CSA C22.2 No. 42	Warranty Type	1-Year
Type	Plug		

### Technical Information

Connector Style	Locking	Flanged	No
-----------------	---------	---------	----

Number of Wires	3	Amperage	30 A
Indoor/Outdoor	Indoor	Voltage	250.0 V
Environmental Conditions	Consult the Factory		