



Control 30A 125/250V Turnlok®



Features & Benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007333312	Country Of Origin	Mexico
Features	Corrosion Resistant	Application Sector	Industrial
Standard	UL498, CSA C22.2 No. 42	Warranty Type	1-Year
Type	Connector		

Technical Information

Connector Style	Locking	Flanged	No
-----------------	---------	---------	----

Number of Wires	3	Amperage	30 A
Indoor/Outdoor	Indoor	Voltage	125/250 V
Environmental Conditions	Consult the Factory		