



Pass and Seymour
30 Amp Non-NEMA Plug, Yellow
Part No. 3431G

Lock Plug Non-nema 3pole 4wire 30amp 250/600volt 3phase-y - For replacement use only.



Features & Benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire. Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock. Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material. Rounded back contour reduces snags and hang-ups on the job site.
- Scalloped shell design provides non-slip gripping surface for insertion and withdrawal. Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention. Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

Color	Black	UPC Number	785007121018
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Industrial	Standard	Non-NEMA

Technical Information

Number of Poles	3-Way	Voltage	3 V, 250 V
Phase	3	Wire Size	#18 - #8
Number of Wires	4	Environmental Conditions	Consult the Factory