



Connector 4-Wire 30A 120/208Volt Turnlok®



## Features & Benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

## Specifications

### General Info

|                    |                |                   |        |
|--------------------|----------------|-------------------|--------|
| Product Line       | Pass & Seymour | Color             | Black  |
| UPC Number         | 785007343311   | Country Of Origin | Mexico |
| Application Sector | Industrial     | Standard          | UL498  |

### Technical Information

|           |            |                          |                     |
|-----------|------------|--------------------------|---------------------|
| Phase     | Three      | Number of Wires          | 4                   |
| Amperage  | 30 A       | Number of Poles          | 4-Way               |
| Wire Size | 18 - 8 AWG | Environmental Conditions | Consult the Factory |