



Pass and Seymour  
30A 125V 5-30R Straight Blade Single Flush Receptacle, 2-Pole, 3-Wire  
Part No. 3802

Straight Blade Receptacle 2-Pole 3-Wire 30A 125A



Features & Benefits

- Quality Materials.
- Durability.
- Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	China
Application Sector	Residential/Commercial	Standard	UL listed

Dimensions

Product Width US	2.5 in	Product Depth US	2.2 in
Product Height US	3.75 in		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus ListingNumber	140596
cULus Listed	Yes	CSA File Number	16063

Technical Information

Number of Wires	3	Amperage	30 A
-----------------	---	----------	------

Number of Poles	Double Pole	Wire Size	14 - 12 AWG
Voltage	125.0 V		