



Pass and Seymour
50A 125/250V 10-50R Straight Blade Single Surface Receptacle, 3-Pole, 3-Wire
Part No. 385



Straight Blade Receptacle 50A 125/250V 3-Pole 3-Wire

Features & Benefits

- Quality Materials.
- Durability.
- Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China	Standard	UL 498

Dimensions

Product Width US	2.8 in	Product Depth US	2.41 in
Product Height US	5.65 in		

Technical Information

Connection	Non Ground	Number of Wires	3
Amperage	50 A	Number of Poles	3-Way
Wire Size	4	Voltage	125.0 V