



Pass and Seymour
30A 125/250V 14-30R Straight Blade Single Surface Receptacle, 3-Pole, 4-Wire
Part No. 3884



Straight Blade Receptacle 3-Pole 4-Wire 30A 125/250V

Features & Benefits

- Quality Materials.
- Durability.
- Time-tested Design.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China	Standard	UL 498

Dimensions

Product Width US	2.8 in	Product Depth US	2.41 in
Product Height US	5.65 in		

Technical Information

Connection	Wire Ground	Number of Wires	4
Amperage	30 A	Number of Poles	3-Way
Wire Size	4	Voltage	125.0 V