



Pass and Seymour
Hospital Grade Quad Receptacles
Part No. 420HGRY

Hospital Grade Quad Receptacle 20A 125V



Features & Benefits

Rugged nylon face and body withstands impacts and hard use.

Built-in wire stripping gauge.

Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.

Heavy-duty, phosphor bronze contacts.

Shielding walls guard against live-circuit-to-ground shorts.

Split circuit break-off tabs.

UL and CSA listed.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007496338	Country Of Origin	Mexico
Number of Receptacles	4	Features	Impact Resistant
Outlet Type	Hospital Grade	Application Sector	Commercial, Healthcare
Wall Plate Included	No	Standard	UL 498, 1449
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	4.5 in
------------------	--------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16063
------------	-----	-----------------	-------

Technical Information

Connection Location	Back and Side	Phase	Three
Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 12 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
Mounting Type	Box	Wire Connection Type	Screw Terminals
Voltage	125.0 V		