

Receptacle Single 15A 250V Turnlok®



Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007456004
Country Of Origin	Mexico	Application Sector	Industrial
Standard	UL 498		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	NO
------------	-----	-----------------	----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Phase	Single-Phase	Number of Wires	3
Number of Poles	Double Pole	Wire Size	0-18 AWG
Voltage	250 V		
