



CC Commercial Grade Connector 15A Yellow

Features & Benefits

All nylon construction.

Termination saddle clamps securely capture stranded wires.

All yellow, perfect for high-visibility cords.

External cord grips are one-size-fits-all, no inserts or flipping the clamps to fit the proper cord OD.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------|--------------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Yellow |
| UPC Number | 785007046045 | Country Of Origin | China |
| Features | Chemical Resistant | Application Sector | Commercial |
| Standard | UL 498 | Warranty Type | 1-Year |
| Type | Connector | | |

Dimensions

| | |
|------------------|----------|
| Product Width US | 1.563 in |
|------------------|----------|

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|------------------------|-------------------|-------------------------|-------------|
| Connector Style | Straight Blade | Flanged | No |
| Terminal Accommodation | #14 AWG - #12 AWG | Number of Wires | 3 |
| Amperage | 15 A | Number of Poles | Double Pole |
| Indoor/Outdoor | Indoor | NEMA Configuration Code | 5-15R |
| Voltage | 125.0 V | | |