



Pass and Seymour
Discontinued - Surge Protective Duplex Receptacle, Blue
Part No. 5252BLSP

Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (LED Indicator only). Back and Side Wire, 15amp 125volt, Blue.

Features & Benefits

Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.

LED Indication: Steady green = protected, Flashing re = not protected, OFF = no power to unit

Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation.

Impact-resistant thermoplastic exterior resists impacts and scrapes.

Triple-wipe, copper-alloy contacts for superior, more dependable connection.

External screw-pressure-plate back and side wire terminals, including ground, with exclusive back wire clamps accept #14-#10 AWG copper or copper-clad, solid or stranded conductors. Pressure plate allows two conductors to be terminated by a single screw.

Thermal protection in 3 modes. Three 17mm dual pack MOVs absorb up to 340 Joules per leg (L-N, L-G, N-G) with 24,000 amp current handling for full, equal, and symmetrical protection. Response time is less than one nanosecond.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	5262BLSP
Color	Blue	UPC Number	785007194425
Country Of Origin	Mexico		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Amperage	15 A
----------	------