



Pass and Seymour
15A 125V Extra Heavy Duty Spec-Grade Surge Protective Duplex Receptacle, Red
Part No. 5262REDSP



Surge Protective Extra Heavy-Duty Duplex Receptacle offers increased transient protection, reliability and protection notification (with Audible Alarm and LED Indicator). Back and Side Wire, 15A, 125V.

Features & Benefits

Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.

Audible alarm alert of MOV damage. Alarm able to be turned On/Off.

Impact-resistant thermoplastic exterior resists impacts and scrapes.

Thermal protection in 3 modes. 3 17mm dual pack MOVs absorb up to 340 Joules of excess energy in each leg (L-N, L-G, N-G) with 24,000 amp current handling capability for full, equal and symmetrical protection.

For covering patents, see www.legrand.us/patents.

Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.

Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation.

Triple-wipe, copper-alloy contacts for superior, more dependable connection.

Protection response time in less than one nanosecond.

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007528022	Country Of Origin	Mexico
Application Sector	Commercial, Residential	Standard	UL 498, 1449

Dimensions

Product Width US	1.7 in	Product Depth US	0.875 in
Product Height US	2.75 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Phase	Three	Class	IG
-------	-------	-------	----

Amperage	15 A		
----------	------	--	--
