



Heavy-Duty Spec Grade Single Receptacle Side-Wire 20A 125V

## Features & Benefits

Auto-ground clip assures positive ground.

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

Backed-out tri-drive steel terminal screws.  
Internal screw-pressure-plate side wire capability.

One-piece brass triple-wire power contacts for lasting retention.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

|                    |                        |                   |        |
|--------------------|------------------------|-------------------|--------|
| Product Line       | Pass & Seymour         | Color             | White  |
| UPC Number         | 785007535150           | Country Of Origin | Mexico |
| Application Sector | Residential/Commercial | Standard          | UL 498 |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Technical Information

|            |             |                 |   |
|------------|-------------|-----------------|---|
| Connection | Wire Ground | Number of Wires | 3 |
|------------|-------------|-----------------|---|

---

Number of Poles

Double Pole

Wire Size

4 AWG

---

Voltage

125 V

---