



Pass and Seymour
20A, 125V Half-Controlled Plug Load Controllable Receptacle, Ivory
Part No. 5362CHI



Permanent controlled receptacle marking allows for long-lasting, easy identification of controlled receptacle for end-users. NEMA-approved and compliant with 2014 NEC, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1.

Features & Benefits

Can be wired to any number of system-based or stand-alone plug load control solutions.

Factory-broken split-circuit tab allows for 50% plug load control to be achieved in one duplex receptacle.

Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face.

8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.

Terminal compartments isolated from each other for positive conductor containment.

Tri-drive terminal and mounting screws.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

| | | | |
|--------------|----------------|-------------------|--------|
| Product Line | Pass & Seymour | Color | Ivory |
| UPC Number | 785007038255 | Country Of Origin | Mexico |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|