



Pass and Seymour

Discontinued - Heavy Duty Spec Grade Single Receptacles, Side Wire Right Angle Slots, 20A, 125V, Brown
Part No. 5371

Heavy-Duty Spec Grade Single Receptacle, Side-Wire Right Angle Slots, 20A 125V.



Features & Benefits

Auto-ground clip assures positive ground.

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

Backed-out tri-drive steel terminal screws.

One-piece brass triple-wipe power contacts for lasting retention.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-------------------|-------------------------|-------------------------|--------------|
| Product Line | Pass & Seymour | Replaced by Part Number | 5351 |
| Color | Brown | UPC Number | 785007537109 |
| Country Of Origin | Mexico | Application Sector | Commercial |
| Standard | UL498, CSA C22.2 No. 42 | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|-----------------|-------|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
| CSA File Number | 16063 | | |

Technical Information

| | | | |
|---------------------|--------------------------|--------------------|--------------|
| Dielectric Strength | Withstands 2000V minimum | Connection | Side Wire |
| Number of Wires | 3 | Temperature Rating | -40° - 60° C |

| | | | |
|-----------|-------------|--------------------------|-----------------------|
| Amperage | 20 A | Number of Poles | Double Pole |
| Wire Size | 14 - 10 AWG | Environmental Conditions | Flammability: UL94 V2 |