



Heavy-Duty Spec Grade Single Receptacle, Side-Wire Right Angle Slots, 20A 125V.



## Features & Benefits

Auto-ground clip assures positive ground.

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

Backed-out tri-drive steel terminal screws.

One-piece brass triple-wipe power contacts for lasting retention.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

|                    |                        |                         |               |
|--------------------|------------------------|-------------------------|---------------|
| Product Line       | Pass & Seymour         | Replaced by Part Number | 5351I         |
| Color              | Ivory                  | Country Of Origin       | Mexico        |
| Application Sector | Residential/Commercial | Standard                | UL 498, WC596 |

### Listing Agencies / 3rd Party Agencies

|                 |       |              |     |
|-----------------|-------|--------------|-----|
| CSA Listed      | Yes   | cULus Listed | Yes |
| CSA File Number | 16063 |              |     |

### Technical Information

|           |             |                 |             |
|-----------|-------------|-----------------|-------------|
| Phase     | 3           | Number of Wires | 3           |
| Amperage  | 20 A        | Number of Poles | Double Pole |
| Wire Size | 14 - 10 AWG | Voltage         | 125.0 V     |

