

Side mount Deep box - same as 55020 with 5 top knockouts and rotating dual support. 24-Pack.



Features & Benefits

Direct mount to joist.	UL listed for fan and fixture support.
Peel-off tape for "hands-free" installation.	Broadest line available, from shallow to deep boxes.
Ground screw pre-installed.	Supplied with hardware.
Boxes include top knockouts.	21 cubic inch volume.
2 inch depth.	Rated up to 70 pounds for fans, 150 pounds for fixture at 16" span.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007266900	Country Of Origin	China
Features	Fan Rated, Fixture Rated	Number of Knockouts	4
Application Sector	Commercial, Residential	Standard	Residential/Commercial
Warranty Type	1-Year Limited Warranty	Type	Ceiling Box

Dimensions

Product Depth US	2.0 in	Cubic Capacity	21 in ³
------------------	--------	----------------	--------------------

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Cable Entry	Back, Side	Box Shape	Round
Mounting Type	Stud Mount		