

Direct Mount Box - with rotating dual support. 24-Pack.



Features & Benefits

Direct mount to joist.

Peel-off tape for "hands-free" installation.

Broadest line available, from shallow to deep boxes.

Supplied with hardware.

Rated up to 70 pounds for fans, 150 pounds for fixture at 16" span.

16 cubic Inch volume.

UL listed for fan and fixture support.

Maximum weight ratings (slides and braces)

Ground screw pre-installed.

Boxes include top knockouts.

1.5" depth.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	China	Features	Fan Rated, Fixture Rated
Number of Knockouts	4	Application Sector	Commercial, Residential
Warranty Type	1-Year Limited Warranty	Type	Ceiling Box

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Cable Entry	Back, Side	Box Shape	Round
Mounting Type	Stud Mount		