



Quiktron  
Q-Series Patch Cords, CAT6, Non-Booted, White, 8 FT  
Part No. 566-125-008



Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.

## Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

## Specifications

### General Info

|               |                   |                    |                        |
|---------------|-------------------|--------------------|------------------------|
| Product Line  | Quiktron          | Color              | White                  |
| UPC Number    | 884815783309      | Country Of Origin  | Vietnam                |
| Features      | Standard Diameter | Application Sector | Commercial, Industrial |
| Warranty Type | 5-Year            | Type               | Copper Patch Cord      |

### Dimensions

|                   |        |                   |        |
|-------------------|--------|-------------------|--------|
| Product Weight US | 0.2 lb | Product Length US | 8.0 FT |
| Cable Length      | 8 ft   |                   |        |

### Additional Information

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

### Technical Information

|                             |                           |                           |                           |
|-----------------------------|---------------------------|---------------------------|---------------------------|
| Jacket Material             | PVC                       | Operating Temperature Min | -10 °C                    |
| Category Performance Rating | Cat6                      | Compatibility             | RJ-45                     |
| Wire Gauge                  | 24 AWG                    | Storage Humidity          | 0-90% RH (Non-Condensing) |
| Plating Specification       | 50 µ in Gold              | Jacket Application        | Riser Rated               |
| Bend Radius                 | 0.896 in                  | Shielded/Unshielded       | Unshielded                |
| Termination Style           | Pre-Terminated            | Conductor Stranding       | Stranded                  |
| Operating Temperature Max   | 60 °C                     | Cable Type                | Non-Booted                |
| Jacket Rating               | CM Rated                  | Cable Diameter            | 0.224 in                  |
| Braid                       | Non-braided Wiring        | Connector 2               | RJ-45 Male                |
| Connector 1                 | RJ-45 Male                | Operating Temperature     | -10°-60°C                 |
| Operating Humidity          | 0-90% RH (Non-Condensing) | Conductor Material        | Copper                    |
| Voltage                     | 300.0 V                   | Storage Temperature       | -40° - 60° C              |