



Pass and Seymour
Industrial Extra Heavy Duty Spec Grade Receptacles, Back and Side Wire, 15A, 250V, Ivory
Part No. 5662AI



Industrial Extra Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 15A 250V

Features & Benefits

One-piece brass mounting strap with integral ground.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Two drive screws anchor strap to back body and face.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face and back body.

Oversized #10 deep tri-drive head brass terminal and ground screws.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

Line terminals accept #14 -- #10 AWG stranded or solid copper clad conductors.

Auto-ground clip assures positive ground.

Corrosion-resistant models have nickel-plated straps and contacts.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007528251	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL 498, WC596

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Phase	3	Number of Wires	3
-------	---	-----------------	---

Number of Poles	Double Pole	Wire Size	10-14Awg
-----------------	-------------	-----------	----------

Voltage	250 V
---------	-------
