



Industrial Extra Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 15amp 250volt Red

Features & Benefits

One-piece brass mounting strap with integral ground.

Two drive screws anchor strap to back body and face.

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and back body.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Line terminals accept #14 -- #10 AWG stranded or solid copper clad conductors.

Corrosion-resistant models have nickel-plated straps and contacts.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Oversized #10 deep tri-drive head brass terminal and ground screws.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	White	UPC Number	785007528299
Country Of Origin	Mexico	Product Line	Pass & Seymour

Application Sector	Residential/Commercial	Standard	UL 498, WC596
--------------------	------------------------	----------	---------------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	250 V
-----------------	-------------	---------	-------

Phase	3	Wire Size	10-14Awg
-------	---	-----------	----------

Number of Wires	3
-----------------	---
