



Heavy-Duty Spec Grade Single Receptacle, Side Wire 20amp 250volt, White

Features & Benefits

Auto-ground clip assures positive ground.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

One-piece brass triple-wire power contacts for lasting retention.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Backed-out tri-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	Ivory	UPC Number	785007585117
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Standard	UL 498

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	250 V
-----------------	-------------	---------	-------

Connection	Wire Ground	Wire Size	4 AWG
Number of Wires	3		
