



Pass and Seymour
Short Strap Spec Grade Single Receptacle, Side Wire, 20A, 250V, Brown
Part No. 5858



Short Strap Spec Grade Single Receptacle, Side Wire, 20amp 250volt, White.

Features & Benefits

Auto-ground clip assures positive ground.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

One-piece brass triple-wipe power contacts for lasting retention.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Backed-out tri-drive steel terminal screws.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	Brown	UPC Number	785007585803
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16063
------------	-----	-----------------	-------

Technical Information

Number of Poles	Double Pole	Voltage	250 V
Connection	Back and side wire	Dielectric Strength	Withstands 2000V minimum
Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	Wire Size	#14 - #10
Number of Wires	3	Environmental Conditions	Flammability: UL94 V2