



Straight Blade Plug 20A 250V Dead Front

## Features & Benefits

All nylon construction, provides excellent impact and chemical resistance.

Ready-to-wire from factory, saves time and money.

Internal finger grips automatically adjust to securely grip the cord jacket.

Simple turn and twist assembly for quick installation.

All black, perfect for stage and entertainment applications.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007586411	Country Of Origin	Mexico
Features	Chemical Resistant, Durable	Application Sector	Commercial
Standard	UL 498	Warranty Type	1-Year
Type	Plug		

### Dimensions

Product Width US	1.53 in	Product Length US	1.64 in
------------------	---------	-------------------	---------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connector Style	Straight Blade	Flanged	No
Terminal Accommodation	#14 AWG - #10 AWG	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	6-20P
Voltage	250.0 V		