



Pass and Seymour  
20A, 125V Watertight Straight Blade, Duplex Receptacle, Black  
Part No. 60W33DPLX



P&S watertight receptacles feature impact-resistant Valox lids, cover plates and receptacle bodies that withstand impacts, chemical and corrosion. Ideal for the harsh environments typically found in food & beverage processing plants, petrochemical plants, marinas & shipbuilding locations, mining locations, mills and more.

## Features & Benefits

Impact-resistant Valox lid, cover plate and receptacle body withstand impacts, chemicals and corrosion.

Stainless-steel hinge spring and pin ensure corrosion resistance.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Spring-loaded flip cover provides protection when device is not in use.

Lockout/tagout capability.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007108910	Country Of Origin	United States
Application Sector	Commercial	Standard	UL Listed, CSA Listed

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Dielectric Strength	Connectors: 2000V AC if rated 300V or less, 3000V AC if rated above 300V. Plugs: 2500V AC if rated 300V or less, 3500V AC if rated above 300V.	Phase	Single
Connection	Screw terminals	Number of Wires	3

---

Temperature Rating	-40°C (without impact) to +60°C continuous	Number of Poles	Double Pole
--------------------	--	-----------------	-------------

---

Wire Size	#14 -#10 AWG Copper Conductor Only	Voltage	125 V
-----------	------------------------------------	---------	-------

---

Environmental Conditions	UL94 HB
--------------------------	---------

---