

Direct Mount Box with rotating dual support. 50 pack.



Features & Benefits

Direct mount to joist.

Peel-off tape for "hands-free" installation.

Broadest line available, from shallow to deep boxes.

Supplied with hardware.

Rated up to 70 pounds for fans, 150 pounds for fixture at 16" span.

1.5" depth.

UL listed for fan and fixture support.

Maximum weight ratings (slides and braces)

Ground screw pre-installed.

Boxes include top knockouts.

16 cubic inch volume.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	China	Features	Fan Rated, Fixture Rated, Rotating Dual Supports
Application Sector	Commercial, Residential	Warranty Type	1-Year Limited Warranty
Type	Ceiling Box		

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Cable Entry	Back	Box Shape	Round
Mounting Type	Stud Mount		