



Slide fan support - same heavy-duty slide as 55501, but with 2.0-inch deep box , to accommodate up to 1-inch firewall or soundproofed ceilings, with rotating dual support for 16-24-inch spans, bulk packed. 25-Pack.

Features & Benefits

For spans from 16 to 24 inches.

Peel-off tape for "hands-free" installation.

Broadest line available, from shallow to deep boxes.

Boxes include top knockouts.

UL listed for fan and fixture support.

Maximum weight rating shown for 16 inch spans.

Pre-assembled with ground screw installed.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007266894	Country Of Origin	China
Features	Fan Rated, Fixture Rated	Number of Knockouts	2
Application Sector	Commercial, Residential	Standard	Residential/Commercial
Warranty Type	1-Year Limited Warranty	Type	Ceiling Box

Dimensions

Product Depth US	2.0 in	Cubic Capacity	21 in³
------------------	--------	----------------	--------

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Cable Entry	Back	Box Shape	Round
Mounting Type	Stud Mount		