Pass and Seymour
**Turnlok® 65W34DPLX Watertight Single Receptacle, Yellow**
Part No. 65W34DPLX

Turnlok Watertight Duplex Receptacle, 15amp 277volt, NEMA Configuration L7-15, Impact resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical, and corrosion.

## Features & Benefits

Impact Resistant Valox lid, cover plate, and receptacle body withstand impacts, chemical & corrosion.

Stainless steel hinge spring and pin for corrosion resistance.

Spring loaded flip covers provide protection when device is not in use.

For Covering Patents, see www.legrand.us/patents.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Yellow |
| Country Of Origin | United States | Standard | UL Listed, CSA Listed |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 1.85 in | Product Depth US | 4.03 in |
| Product Height US | 1.85 in | | |

### Technical Information

| | | | |
|---|---|---|---|
| Phase | Single | Number of Wires | 3 |
| Amperage | 15 A | Number of Poles | Double Pole |
| Wire Size | 18 - 12 AWG | Voltage | 277.0 V |

| | |
|---|---|
| Environmental Conditions | Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized |